



Features

- Compliant with AEC-Q200 Rev-C - Stress Test Qualification for Passive Components in Automotive Applications
- Small footprint size (1206)
- Operating temperature range up to 125 °C
- Low thermal derating factor
- Higher hold currents at elevated temperatures
- RoHS compliant*

Applications

- Protection of automotive circuitry including engine control modules
- Overcurrent surge protection of electronic equipment required to operate at high operating temperature ranges
- Resettable fault protection for general electronic equipment

MF-NSHT Series - PTC Resettable Fuses

Electrical Characteristics

Model	V max. Volts	I max. Amps	I _{hold}	I _{trip}	Resistance		Max. Time To Trip		Tripped Power Dissipation
			Amperes at 23 °C		Ohms at 23 °C		Amperes at 23 °C	Seconds at 23 °C	Watts at 23 °C
			Hold	Trip	R _{Min.}	R _{1Max.} **			Typ.
MF-NSHT016KX	30	80	0.16	0.80	0.7	6.0	8.0	0.1	0.9
MF-NSHT035KX	30	80	0.35	1.75	0.4	2.6	8.0	0.1	0.9

**R_{1Max.} measured 24 hours post reflow.

Environmental Characteristics

Operating Temperature.....	-40 °C to +125 °C	
Passive Aging.....	+125 °C, 1000 hours.....	R _{final} < R _{1max.}
Humidity Aging.....	+85 °C, 85 % R.H. 1000 hours	R _{final} < R _{1max.}
Thermal Shock	+125 °C to -40 °C, 20 times.....	R _{final} < R _{1max.}
Solvent Resistance.....	MIL-STD-202, Method 215	No change
Vibration	MIL-STD-883C, Method 2007.1.....	No change
	Condition A	
Moisture Sensitivity Level (MSL)	Level 1	
ESD Classification - HBM.....	Class 6	

Test Procedures And Requirements For Model MF-NSHT Series

Test	Test Conditions	Accept/Reject Criteria
Visual/Mech.	Verify dimensions and materials	Per MF physical description
Resistance.....	In still air @ 23 °C	R _{min} ≤ R ≤ R _{1max}
Time to Trip.....	At specified current, V _{max} , 23 °C.....	T ≤ max. time to trip (seconds)
Hold Current	30 min. at I _{hold}	No trip
Trip Cycle Life.....	V _{max} , I _{max} , 100 cycles.....	No arcing or burning
Trip Endurance	V _{max} , 48 hours.....	No arcing or burning
Solderability	ANSI/J-STD-002	95 % min. coverage

Thermal Derating Chart - I_{hold} (Amps)

Model	Ambient Operating Temperature									
	-40 °C	-20 °C	0 °C	+23 °C	+40 °C	+50 °C	+60 °C	+70 °C	+85 °C	+125 °C
MF-NSHT016KX	0.232	0.210	0.186	0.160	0.141	0.130	0.118	0.107	0.090	0.043
MF-NSHT035KX	0.508	0.459	0.406	0.350	0.308	0.284	0.259	0.235	0.196	0.095

BOURNS®

Asia-Pacific: Tel: +886-2 2562-4117 • Email: asiacus@bourns.com

EMEA: Tel: +36 88 520 390 • Email: eurocus@bourns.com

The Americas: Tel: +1-951 781-5500 • Email: americus@bourns.com

www.bourns.com

*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

MF-NSHT Series - PTC Resettable Fuses


BOURNS®

Product Dimensions

Model	A		B		C		D
	Min.	Max.	Min.	Max.	Min.	Max.	Min.
MF-NSHT016KX	$\frac{3.00}{(0.118)}$	$\frac{3.40}{(0.134)}$	$\frac{1.40}{(0.055)}$	$\frac{1.80}{(0.071)}$	$\frac{0.40}{(0.016)}$	$\frac{0.85}{(0.033)}$	$\frac{0.25}{(0.010)}$
MF-NSHT035KX	$\frac{3.00}{(0.118)}$	$\frac{3.40}{(0.134)}$	$\frac{1.40}{(0.055)}$	$\frac{1.80}{(0.071)}$	$\frac{0.40}{(0.016)}$	$\frac{0.85}{(0.033)}$	$\frac{0.25}{(0.010)}$

Packaging: 3000 pcs. per reel.

DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$



Terminal material:

Nickel/gold plated.

Termination pad solderability:


Standard Au finish:

Meets ANSI/J-STD-002 Category 2.

Recommended Storage:

40 °C max./70 % RH max.

Typical Time to Trip at 23 °C



The Time to Trip curves represent typical performance of a device in a simulated application environment. Actual performance in specific customer applications may differ from these values due to the influence of other variables.


How to Order

MF - NSHT 016 K X - 2

Multifuse® Product Designator _____
 Series _____
 NSHT = 1206 High Temperature Surface Mount Component
 Hold Current, I_{hold} _____
 016 - 035 (0.16 - 0.35 Amps)
 Material Specific Code _____
 Multifuse® freeXpansion™ Design _____
 Packaging _____
 Packaged per EIA 481-1
 -2 = Tape and Reel

Typical Part Marking

Represents total content. Layout may vary.




BIWEEKLY DATE CODE WILL APPEAR ON THE PACKAGING LABEL:
 WEEK 1 AND 2 = A
 WEEK 51 AND 52 = Z

MF-NSHT Series - PTC Resettable Fuses

BOURNS®

Solder Reflow Recommendations



Notes:

- MF-NSHT models cannot be wave soldered or hand soldered. Please contact Bourns for soldering recommendations.
- All temperatures refer to topside of the package, measured on the package body surface.
- If reflow temperatures exceed the recommended profile, devices may not meet the published specifications.
- Compatible with Pb and Pb-free solder reflow profiles.
- Excess solder may cause a short circuit, especially during hand soldering. Please refer to the Multifuse® Polymer PTC Soldering Recommendation guidelines.
- Designed for single solder reflow operations.


Profile Feature	Pb-Free Assembly
Average Ramp-Up Rate (TS _{max} to Tp)	3 °C / second max.
PREHEAT: Temperature Min. (TS _{min}) Temperature Max. (TS _{max}) Time (ts _{min} to ts _{max})	150 °C 200 °C 60~180 seconds
TIME MAINTAINED ABOVE: Temperature (TL) Time (tL)	217 °C 60~150 seconds
Peak / Classification Temperature (Tp)	260 °C
Time within 5 °C of Actual Peak Temperature (tp)	20~40 seconds
Ramp-Down Rate	6 °C / second max.
Time within 25 °C to Peak Temperature	8 minutes max.

MF-NSHT Series Tape and Reel Specifications

BOURNS®

Tape Dimensions		MF-NSHT Series per EIA 481-1
W		8.0 ± 0.30 (0.315 ± 0.012)
P ₀		4.0 ± 0.10 (0.157 ± 0.004)
P ₁		4.0 ± 0.10 (0.157 ± 0.004)
P ₂		2.0 ± 0.05 (0.079 ± 0.002)
A ₀		1.95 ± 0.10 (0.077 ± 0.004)
B ₀		3.55 ± 0.10 (0.140 ± 0.004)
B ₁ max.		4.35 (0.171)
D ₀		$1.5 + 0.10/-0.0$ (0.059 + 0.004/-0)
F		3.5 ± 0.05 (0.138 ± 0.002)
E ₁		1.75 ± 0.10 (0.069 ± 0.004)
E ₂ min.		6.25 (0.246)
T max.		0.6 (0.024)
T ₁ max.		0.1 (0.004)
K ₀		0.80 ± 0.15 (0.031 ± 0.006)
Leader min.		390 (15.35)
Trailer min.		160 (6.30)
Reel Dimensions		
A max.		185 (7.28)
N min.		50 (1.97)
W ₁		$8.4 + 1.5/-0.0$ (0.331 + 0.059/-0.0)
W ₂ max.		14.4 (0.567)

DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$



Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.